



## 50m USB 2.0 Cat.5 Extender

Part No.: 42693

### Description

- Extends a single USB port up to 50m using low cost Cat.5e/6 network cable (not included)
- Plug & Play installation, OS independent
- Perfect for use with USB 2.0 devices such as storage devices, printers, scanners, mice and keyboards
- Supports USB 2.0 High Speed and USB 1.1 Full Speed / Low Speed
- 2 year warranty

The Lindy 50m USB 2.0 Cat.5 Extender can be used to extend the distance between a USB peripheral device and host computer by up to 50m. It consists of a local unit which connects to the computer and a remote unit that connects to the device. Standard, low cost Cat.5e/6 network cable (not included) is then used to bridge the connection between the two units.

Connecting a USB hub to the receiver also gives additional access to a larger number of USB devices. For added convenience this USB 2.0 Extender is supplied with a power supply, which can be connected should additional power be required.

### Technical details

#### Specifications

- USB Standard: USB 2.0
- Supported Bandwidth: 480Mbps
- Maximum Distance: 50m (164.04ft)
- Transmission Medium: Cat.5/5e/6 or higher network cable
- Chipset: LG-8311
- Special Features: -

## Connectors

- Transmitter Input: USB Type A (Male)
- Transmitter Output: RJ45 (Female)
- Receiver Input: RJ45 (Female)
- Receiver Output: USB Type A (Female)
- Power: 3.5/1.35mm DC socket

## Physical Properties

- Dimensions WxDxH: 30x60x15mm (1.18x2.36x0.59in)
- Housing Material: Plastic
- Net Weight: 0.064kg (0.14lb)
- Operating Temperature: -0° - 70°C (32°F - 158°F)
- Storage Temperature: -20°C - 80°C (-4°F - 176°F)
- Humidity: 0 - 90% RH (non-condensing)
- Power Requirements: 5VDC 2.1A
- Colour: Black

## Miscellaneous

- Packaging Type: Carton Box
- Packaging Dimensions: 140x130x85mm (5.51x5.12x3.35in)
- Gross Weight: 0.235kg (0.52lb)
- Warranty (Years): 2
- Certificated: CE, FCC, RoHS & REACH

## Package content

- Transmitter unit
- Receiver unit
- Multi-Country Power Supply (EU, UK, US & AUS)
- Lindy Manual

## Purchasing information

- No.: 42693
- EAN: 4002888426930