



3m USB 2.0 Type A to B Cable, Cromo Line

Part No.: 36643

Description

- Superior performance and design USB 2.0 Type A to B cable
- Supports data transfer speeds up to 480Mbps
- Chrome design ABS housing, gold plated connectors and contacts
- Double shielded cable, corrosion resistant, high performance tinned copper conductors
- USB 2.0, 480Mbps; 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Cromo Line USB 2.0 Type A to B cables are high performance, designer connections that combine premium construction with striking connector architecture.

Cromo Line USB 2.0 cables feature double shielded construction with tinned copper conductors for premium performance and corrosion resistance. High quality gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

Data transfer speeds up to 480Mbps are supported for the quick and effortless transfer of large data volumes.

Cromo Line USB 2.0 Type A to B cables are available in lengths from 0.5m, 1m, 2m, 3m, 5m and 7.5m.

Technical details

Connectors

- Connector A: USB 2.0 Type A Male
- Connector B: USB 2.0 Type B Male
- Housing Material: Chrome Plated, ABS
- Connector Plating: Gold 1µm
- Pin Construction: Phosphor Bronze
- Pin Plating: Gold 3µm
- Dimensions (approx.) WxDxH:
 - A: 16x35x8.3mm (0.63x1.38x0.34in)
 - B: 11.8x35x10.2mm (0.47x1.38x0.40in)

Cable Construction

- Length: 3m (9.84ft)
- Standard: USB 2.0
- Colour: Grey
- Type: Round
- Jack Diameter: 4.6mm (0.18in)
- Jack Material: PVC
- Conductor Material: Tinned Copper
- Conductor Gauge: 24/28AWG
- Shielding: Copper Braid 85%

Specifications

- Supported Bandwidth: 480Mbps
- Maximum Resolution: -
- Maximum Colour depth: -
- Nominal Attenuation:
 - 0.5-5m: 0.5-400MHz < 5.8db
 - 7.5m: 0.5-400MHz < 7.0db
- Minimum Bend Radius: 55mm (2.2in)
- Operating Temperature: -20°C - 80°C (-4°F - 176°F)
- Storage Temperature: -25°C - 85°C (-13°F - 185°F)
- ATC Approved: -

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH, UL

Purchasing Information

- No.: 36643
- EAN: 4002888366434

This product is also available in other lengths

- 36640 - 0.5m (1.64ft)
- 36641 - 1m (3.28ft)
- 36642 - 2m (6.56ft)
- 36643 - 3m (9.84ft)
- 36644 - 5m (16.44ft)
- 36645 - 7.5m (24.61ft)

© LINDY 2019