



2m Cat.6 S/FTP Cable

Part No.: 47344

Description

- Twisted Pair Patch Cable with RJ45 connectors
- Cat.6 S/FTP PIMF, PVC
- Integrated snagless connector for latch protection
- Gold plated pins for better conductivity and elimination of signal loss
- 10 year warranty

Lindy's Cat.6 Patch Cables are manufactured and tested to conform with the ISO 11801 specification. A robust snagless strain relief design prevents damage

to the connector latch during installation and removal. Gold plated pins ensure complete signal integrity no matter the application.

Each cable is packaged in a polybag, Cables of various colours are also available and therefore ideally suited for structured cabling in server cabinets or wall cabinets.

RJ45 connectors offer universal connectivity to computers and network components, such as routers, switches, network printers and network attached storage devices.

These cables are also ideal for use in data centres, rack spaces, server rooms and network cabinets. Additional uses include security systems and AV installations.

Technical details

Connectors

- Connector A: RJ45 Male
- Connector B: RJ45 Male
- Housing Material: Polycarbonate

- Connector Plating: Nickel
- Pin Construction: Copper
- Pin Plating: Gold plated
- Dimensions (approx.) WxDxH: 22.8x11.6x8.3mm (0.90x0.46x0.33in)

Cable Construction

- Length: 0.3m (0.98ft)
- Colour: Grey
- Type: Cat.6
- Jacket Diameter: 6.2mm (0.24in)
- Jacket Material: PVC
- Conductor Material: Copper
- Conductor Gauge: 28AWG
- Shielding: Aluminium Braid

Specifications

- Supported Bandwidth: 250MHz
- Nominal Attenuation: 32.8dB/100m @250MHz
- Minimum Band Radius: 74mm (2.91in)
- Operating Temperature: -10°C - 60°C (14°F - 140°F)
- Storage Temperature: -20°C - 75°C (-4°F - 167°F)

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH, UL, California Proposition 65

Purchasing Information

- No.: 47340
- EAN: 4002888473408

This product is also available in other lengths

- 47340 - 0.3m (0.98ft)
- 47341 - 0.5m (1.64ft)
- 47342 - 1m (3.28ft)
- 47343 - 1.5m (4.92ft)
- 47344 - 2m (6.56ft)
- 47345 - 3m (9.84ft)
- 47346 - 5m (16.44ft)
- 47347 - 7.5m (24.61ft)
- 47348 - 10m (32.81ft)

