



Basic Cat.6 S/FTP Cable, Black, 5m

Part No.: 47376

Description

- Full CAT6 specification with moulded boots and unique connector latch protection
- Gigabit Ethernet ready
- Stranded core cables allowing repeated flexing without damage, prolonging the life of the cable
- S/FTP - (S) Braided cable shielding / (FTP) Foil Twisted Pair, also known as PiMF - Pairs in Metal Foil
- 10 year warranty

The LINDY CAT6 RJ45 S/FTP patch leads are manufactured and tested to conform with ISO 11801 specifications.

The unique snagless strain relief design prevents damage to the connector latch during installation and removal.

Every cable is 100% performance tested and comes with the LINDY “no surprises” guarantee.

These cables are ideal for connecting computers, hubs, switches, print servers and patch panels but are finding more and more uses in AV applications and security cameras.

Technical details

- Standards: ISO/IEC 11801, EN50173, EIA/EIA 568C.2
- Wiring spec: Straight through

- Ethernet standard: 10/100/1000Base-Tx
- Bandwidth: 250Mhz
- Shielding: Yes
- LS0H (Low Smoke Zero Halogen): No
- Corresponds to: ANSI / TIA-568-C.2
- Used according to colour code: TIA / EIA-568-B
- Colour: Black
- Lengths available: 0.3m to 10m