



**0.3m, RJ45 Patch Cable S/FTP LSOH with Cat.7
Rawcable, white**

Part No.: 47320

Description

- Assembled S/FTP Patch Cable
- PIMF cable (pairs in metal foil)
- 10/100 / 1000Base-TX support
- Category 7, 26 AWG, 4 pairs, 600Mhz
- Gigabit compatible, 10GBase-T
- Low Smoke Zero Halogen cable
- Connector: RJ45 shielded, Snagless (jack Protection), gold-plated contacts
- Colour: White
- 10 year warranty

LINDY CAT7 SFTP LS0H PiMF Cables are high quality Category 7 cables.

These cables are ideal for connecting computers, hubs, switches, print servers and patch panels but are finding more and more uses in AV applications and security cameras.

The cables material is composed of thermoplastic compounds that emit limited smoke and no halogen when exposed to high sources of heat. While gold plated contacts help give optimum conductivity as well as resistance to tarnishing and corrosion. This boosts signal integrity and the cables overall performance and longevity.

The RJ-45 connectors offer universal connectivity to computers and network components such as routers, switch boxes, network printers and network attached storage devices; as well as being ideal for use in data centres, rack spaces, server rooms and network cabinets.

The unique snagless strain relief design prevents damage to the connector latch during installation and removal.

Please Note: This cable uses Cat.7 raw cable (600Mhz) and Cat.6A connectors.

For legal reasons its necessary to print "Cat.6A S/FTP patch cords with 600MHz raw cable" on the cable.

Technical details

- Full CAT7 specification with moulded boots and unique connector latch protection.
- Low Smoke Zero Halogen PIMF (Pairs in metal foil) Cable
- 8µm Gold plated pins
- 26AWG Stranded core cables allowing repeated flexing without damage (prolonging the life of the cable)

Certified: UL No. E321484 AVM 2835. ANSI/TIA-568-C.2

© LINDY 2019