



Cat.6 U/UTP Cable, orange, 0.5m

Part No.: 48106

Description

- Full CAT6 specification with moulded boots and unique connector latch protection
- Gigabit Ethernet ready
- Stranded core cables allowing repeated flexing without damage, prolonging the life of the cable
- Useful for colour coding your departments, work-groups, etc.
- 10 year warranty

The LINDY CAT6 RJ45 U/UTP patch leads are manufactured and tested to conform with ISO 11801 specification. The unique snagless strain relief design prevents damage to the connector latch during installation and removal. Every cable is 100% performance tested and comes with the LINDY “no surprises” guarantee.

Technical details

- U/UTP - (U) unshielded cable shielding / (UTP) Unshielded Twisted Pair
- Standards: ISO/IEC 11801, EN50173, EIA/EIA 568B.2
- Wiring spec: Straight through
- Ethernet standard: 10GBase-T
- Bandwidth: 250Mhz
- Shielding: No
- LS0H (Low Smoke Zero Halogen): No
- Colours available: Grey, Yellow, Blue, Red, Green, Orange, Purple, Black, White
- Lengths available: 0.3m to 30m