



7 Port USB 2.0 Metal Hub

Part No.: 42794

Description

- Provides 7 USB 2.0 HighSpeed ports with data rates up to 480Mbps
- Hard-wearing USB Hub - Perfect for industrial applications
- Robust metal housing with high EMC protection and integrated brackets for mounting
- USB bus-powered, or can be externally powered
- 2 years warranty

The Lindy 7 Port USB 2.0 Metal Hub has been designed to provide reliable performance in demanding operating environments. This industrial-grade hub features a rugged, all-metal chassis providing excellent EMC protection.

With robust metal housing and integrated mounting brackets this Hub is the ideal solution for industrial environments.

Each USB port port features individual short circuit protection. The included power supply ensures secure and uninterrupted electricity supplies.

Technical details

Specifications

- USB Standard: USB 2.0
- Supported Bandwidth: 480Mbps
- Chipset: FE 2.1
- Compatibility: USB Type A equipped computers
- Power Delivery: -
- Special Features: Integrated brackets for mounting

Connectors

- Inputs: 1 x USB Type B (Female)
- Outputs: 7 x USB Type A (Female)
- Power: 5.5/2.1mm DC socket

Physical Properties

- Dimensions WxDxH: 165x48x24mm (6.5x1.89x0.94in)
- (Fixed) Cable Length: -
- Housing Material: Metal
- Net Weight: 0.251kg (0.55lb)
- Operating Temperature: 0°C - 50°C (32°F -122°F)
- Storage Temperature: -20°C - 60°C (-4°F -140°F)
- Humidity: 0 - 90% RH (non-condensing)
- Power Requirements: 5VDC 3.5A
- Colour: Black

Miscellaneous

- Packaging Type: Carton Box
- Packaging Dimensions: 222x156x40mm (8.74x6.14x1.57in)
- Gross Weight: 0.648kg (1.43lb)
- Warranty (Years): 2
- Certificated: CE, FCC, RoHS & REACH

Package Content

- 7 Port USB 2.0 Metal Hub
- 1.8m USB 2.0 Type A to B Cable
- Multi-Country Power Supply (EU, UK, US & AU)

Purchasing Information

- No.: 42794
- EAN: 4002888427944