

Schuko to 1x IEC C13 and 1x IEC C5 Y-Cable, 2m

Part No.: 30047



Description

- Y-type power supply cable, plastic, encapsulated
- Connections: Schuko plug to 2 x IEC coupling, 1x C13 cold-plug coupling and 1x C5 (Mickey Mouse, for example for notebook power supply)
- Schuko cord: 1.0mm², approx. 1,8m, cable material H05 VV-F 3G X 1.0mm²
- IEC strands: 1.0 mm², approx. 0.2m, cable material H05 VV-F 3G X 1.0mm²
- 10 year warranty

LINDY power cables are perfect for use in professional areas (recording studios, light systems and also for event locations of any kind, etc.) – but you can also use them in private sections.

Due to the high temperature resistance from -10 to 70°C during operation these cables can also be used in non air-conditioned areas.

Technical details

- Number of wires: 3
- Wire cross-section: 1.50mm²
- Available lengths: 2m
 - Schuko to Y: approx. 1.80m
 - Y to IEC C13 or IEC C5: approx. 0.20m
- Operating temperature: ca. -10 to 70°C
- Storage temperature: ca. -25 to 70°C
- Colour: Black
- 10 years warranty

Note: Only for use in dry areas!

© LINDY 2019