



**IEC Mains lead (German and French), angled, 2m**  
Part No.: 30345

## Description

- Conductor cross section : 3 x 1.00 mm<sup>2</sup>
- Cable Material: H05 VVF 3 G 1:00 mm<sup>2</sup>
- Connector CEE 7/7 ( TYPEF ) Schuko (With capacity for double ground contact) to IEC 320 C13 angled (clutch), 90°
- Length: 2m
- Colour: Black
- 10 year warranty

These LINDY power cables are perfect for the use in professional areas (recording studios, light systems and also for event locations of any kind, etc.) – but you can also use them in private sections.

This angled IEC connector is ideally suited for small and narrow installations such as mounting racks with limited space at the back.

Due to the high temperature resistance from -10 to 70°C during operation, these cables can also be used in non air-conditioned areas.

## Technical details

- Connector A: Schuko
- Connector B: IEC C13, angled
- Cable type: H05-VVF 3G\*1.00mm<sup>2</sup>
- Number of wires: 3

- Wire cross-section: 1.00mm<sup>2</sup>
- Available lengths: 2 - 5m
- Operating temperature: ca. -10 to 70°C
- Storage temperature: ca. -25 to 70°C
- Colour: Black
- 10 years warranty

Note: Only for the use in dry areas!

© LINDY 2019