



30m Cat.6A DVI-D Single Link Extender

Part No.: 32599

Description

- Allows DVI-D video signals to be sent up to 30m using low cost (not included)
- Supports HDTV resolutions of 480i, 576i, 480p, 576p, 720p and 1080p
- HDCP not supported
- Dimensions: 4 x 5 x 2.5cm (WxDxH)
- 2 year warranty

Technical details

Specifications

- AV Interface: DVI-D
- Interface Standard: DVI-D 1.1 (Single Link)
- Supported Bandwidth: 4.95 Gbps
- Maximum Distance:
 - 30m (98.42ft) - 1024x768@60Hz / Cat.6a
 - 20m (65.62ft) - 1680x1050@60Hz / Cat.6
 - 15m (49.21ft) - 1920x1200@60Hz / Cat.6a
- Maximum Resolution: 1920x1200@60Hz
- HDCP Support: -
- EDID Pass Through: -
- Supported Audio: -
- Separate Audio Ports: -
- IR Support: -
- CEC Support: -
- Serial Interface: -
- Transmission Protocol: -
- Transmission Medium: 1 x Cat.6A / Cat.6
- Laser Class (only for Fibre): -
- Wavelength (only for Fibre): -
- Chipset: -
- Special Features: -

Connectors

- Transmitter Input: DVI-D (Male)
- Transmitter Output: RJ45 (Female)
- Receiver Input: RJ45 (Female)
- Receiver Output: DVI-D (Male)
- Bidirectional Ports: -
- Power: -

Physical Properties

- Dimensions WxDxH: 40x50x25mm (1.57x1.97x0.98in) per unit
- Housing Material: Plastic
- Net Weight: 0.028kg (0.06lb) per unit
- Operating Temperature: 0°C - 55°C (32°F - 131°F)
- Storage Temperature: -20°C - 85°C (-4°F - 185°F)
- Humidity: 0 - 95% RH (non-condensing)
- Power Requirements: -
- Colour: Black

Miscellaneous

- Packaging Type: Carton Box
- Packaging Dimensions: 110x165x42mm (4.33x6.5x1.65in)
- Gross Weight: 0.15kg (0.33lb)
- Warranty (Years): 2
- Certificated: CE, FCC, RoHS & REACH

Package Content

- Transmitter unit
- Receiver unit
- Lindy manual

Purchasing Information

- No.: 38599
- EAN: 4002888325998