



IEC Extension Cable, Red, 1m

Part No.: 30477

Description

- Can be used as a power extension cable or a computer / monitor / UPS power connection lead
- IEC C14 to IEC C13
- Fully moulded connectors
- VDE approved
- Length: 1m
- 10 year warranty

These LINDY power cables are perfect for use in professional areas (recording studios, light systems and also for event locations of any kind, etc.) – but you can also use them in private sections.

These cables are available in different colours and are ideally suited for structured cabling in server cabinets or wall cabinets.

Due to the high temperature resistance from -10 to 70°C during the operation these cables can also be used in non air-conditioned areas.

Technical details

- Connector A: IEC C14
- Connector B: IEC C13
- Cable type: H05-VVF 3G*0.75mm²
- Number of wires: 3
- Wire cross-section: 0.75mm²

- Available lengths: 0.5 - 2m
- Operating temperature: ca. -10 to 70°C
- Storage temperature: ca. -25 to 70°C
- Available Colours: Blue, Orange, Red
- 10 years warranty

Note: Only for the use in dry areas!

© LINDY 2019