



CAT6 SFTP / SSTP Snagless PiMF LS0H Network Cable, Grey, 0.3m

Part No.: 45580

Description

- Full CAT6a specification with moulded boots and unique connector latch protection
- Snagless strain relief prevents damage to the RJ-45 latch during installation and removal
- Low Smoke Zero Halogen PIMF (pairs in metal foil) Cable
- 50µ Gold plated pins
- 26AWG Stranded core cables allowing repeated flexing without damage, prolonging the life of the cable
- Ideal for connecting computers, hubs, switches, print servers, patch panels, etc.
- Standards: ISO/IEC 11801, EN50173, EIA/EIA 568B.2
- 100% performance tested
- Color: Grey
- 10 year warranty