

THSW 0°+60°C NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Filter fans and cabinet heaters are ideally complemented by thermostats and hygrostats. Filter fans and heaters only work when cooling or heating is actually necessary. Because of the demand-oriented thermostats and hygrostats increase the energy efficiency and save costs.

General ordering data

Type	THSW 0°+60°C NC
Order No.	2558230000
Version	Temperature switch, grey white
GTIN (EAN)	4050118568882
Qty.	1 pc(s).

THSW 0°+60°C NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	40 mm	Width (inches)	1.575 inch
Height	72 mm	Height (inches)	2.835 inch
Depth	36 mm	Depth (inches)	1.417 inch
Net weight	50 g		

General data

Contact design	1 NC contact	Switching current, NC contact	10 A
Switching current, NC contact, inductive load $\cos \varphi = 0.6$	2 A	Switching difference	<7 K
Switching tolerance	± 4 K	Switching voltage	240 V AC
Temperature setting range, max.	40 °C	Temperature setting range, min.	0.01 °C
Type of connection	Screw connection	Type of mounting	Rail

Classifications

ETIM 6.0	EC002014	eClass 6.2	27-18-07-16
eClass 9.1	27-21-07-07		

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	STEP
User Documentation	Operating instructions