

THSW 0°+60°C NO/NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Filter fans and cabinet heaters are ideally complemented by thermostats and hygrostats. Filter fans and heaters only work when cooling or heating is actually necessary. Because of the demand-oriented thermostats and hygrostats increase the energy efficiency and save costs.

General ordering data

Type	THSW 0°+60°C NO/NC
Order No.	2558250000
Version	Temperature switch, grey white
GTIN (EAN)	4050118568905
Qty.	1 pc(s).

THSW 0°+60°C NO/NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	59 mm	Width (inches)	2.323 inch
Height	80.5 mm	Height (inches)	3.169 inch
Depth	38 mm	Depth (inches)	1.496 inch
Net weight	100 g		

General data

Contact design	1 NC contact, 1 NO contacts	Switching current, NC contact	10 A
Switching current, NC contact, inductive load $\cos \varphi = 0.6$	2 A	Switching current, NO contact	10 A
Switching current, NO contact, inductive load $\cos \varphi = 0.6$	2 A	Switching difference	<7 K
Switching tolerance	± 4 K	Switching voltage	250 V AC / 30 V DC
Temperature setting range, max.	40 °C	Temperature setting range, min.	0.01 °C
Type of connection	Screw connection	Type of mounting	Rail

Classifications

ETIM 6.0	EC002014	eClass 6.2	27-18-07-16
eClass 9.1	27-21-07-07		

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	STEP
User Documentation	Operating instructions