

EF 10 54 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

Type	EF 10 54 BK
Order No.	2557080000
Version	Exhaust filter, IP54, black
GTIN (EAN)	4050118567717
Qty.	1 pc(s).

Data sheet

EF 10 54 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	109 mm	Width (inches)	4.291 inch
Height	109 mm	Height (inches)	4.291 inch
Depth	23 mm	Depth (inches)	0.906 inch
Net weight	60 g		

General data

EMC version	No	Filter class	G 3
Height of installation cut-outs	92 mm	Material	Thermoplastic
Mounting depth	19 mm	Mounting height	4 mm
Type of mounting	Snap-on	Width of installation cut-outs	92 mm
With filter	Yes		

Classifications

ETIM 6.0	EC002513	eClass 6.2	27-18-07-16
eClass 9.1	27-18-07-06		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [STEP](#)