

EF 30 54 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

| | |
|------------|----------------------------|
| Type | EF 30 54 GY |
| Order No. | 2557130000 |
| Version | Exhaust filter, IP54, grey |
| GTIN (EAN) | 4050118567762 |
| Qty. | 1 pc(s). |

Data sheet

EF 30 54 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Width | 202 mm | Width (inches) | 7.953 inch |
| Height | 202 mm | Height (inches) | 7.953 inch |
| Depth | 40 mm | Depth (inches) | 1.575 inch |
| Net weight | 260 g | | |

General data

| | | | |
|---------------------------------|---------|--------------------------------|---------------|
| EMC version | No | Filter class | G 3 |
| Height of installation cut-outs | 177 mm | Material | Thermoplastic |
| Mounting depth | 34 mm | Mounting height | 6 mm |
| Type of mounting | Snap-on | Width of installation cut-outs | 177 mm |
| With filter | Yes | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC002513 | eClass 6.2 | 27-18-07-16 |
| eClass 9.1 | 27-18-07-06 | | |

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [STEP](#)