

**EF 40 55 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Similar to illustration**

The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

**General ordering data**

Type	EF 40 55 GY
Order No.	<a href="#">2557190000</a>
Version	Exhaust filter, IP55, grey
GTIN (EAN)	4050118567823
Qty.	1 pc(s).

**Data sheet**

**EF 40 55 GY**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	252 mm	Width (inches)	9.921 inch
Height	252 mm	Height (inches)	9.921 inch
Depth	44 mm	Depth (inches)	1.732 inch
Net weight	460 g		

**General data**

EMC version	No	Filter class	G 4
Height of installation cut-outs	223 mm	Material	Thermoplastic
Mounting depth	38 mm	Mounting height	6 mm
Type of mounting	Snap-on	Width of installation cut-outs	223 mm
With filter	Yes		

**Classifications**

ETIM 6.0	EC002513	eClass 6.2	27-18-07-16
eClass 9.1	27-18-07-06		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data [STEP](#)