

EF 60 54 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

General ordering data

Type	EF 60 54 GY
Order No.	2557210000
Version	Exhaust filter, IP54, grey
GTIN (EAN)	4050118567847
Qty.	1 pc(s).

Data sheet

EF 60 54 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	320 mm	Width (inches)	12.598 inch
Height	320 mm	Height (inches)	12.598 inch
Depth	46 mm	Depth (inches)	1.811 inch
Net weight	700 g		

General data

EMC version	No	Filter class	G 3
Height of installation cut-outs	291 mm	Material	Thermoplastic
Mounting depth	39 mm	Mounting height	7 mm
Type of mounting	Snap-on	Width of installation cut-outs	291 mm
With filter	Yes		

Classifications

ETIM 6.0	EC002513	eClass 6.2	27-18-07-16
eClass 9.1	27-18-07-06		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [STEP](#)