

**RH-CBCO 10W 110-250V BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

**General ordering data**

Type	RH-CBCO 10W 110-250V BK
Order No.	<a href="#">2557860000</a>
Version	Radiant heating panel, 110 V, 250 V, IP54, black
GTIN (EAN)	4050118568509
Qty.	1 pc(s).

**RH-CBCO 10W 110-250V BK**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	29.5 mm	Width (inches)	1.161 inch
Height	45 mm	Height (inches)	1.772 inch
Depth	75 mm	Depth (inches)	2.953 inch
Net weight	170 g		

**General data**

Continuous heat output at 10°C	10 W	Supply voltage, max	250 V
Supply voltage, min.	110 V	Type of connection	Pre-assembled cable
Type of mounting	Rail	With room thermostat	No

**Classifications**

ETIM 6.0	EC000737	eClass 6.2	27-18-07-16
eClass 9.1	27-18-07-10		

**Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">Operating instructions</a>