

RH-CBCO 30W 110-250V BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The formation of condensation is one of the largest dangers for electrical cabinets. With our cabinet heaters prevention of condensation in the cabinet is guaranteed.

General ordering data

Type	RH-CBCO 30W 110-250V BK
Order No.	2557880000
Version	Radiant heating panel, 110 V, 250 V, IP54, black
GTIN (EAN)	4050118568523
Qty.	1 pc(s).

RH-CBCO 30W 110-250V BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	29.5 mm	Width (inches)	1.161 inch
Height	45 mm	Height (inches)	1.772 inch
Depth	75 mm	Depth (inches)	2.953 inch
Net weight	170 g		

General data

Continuous heat output at 10°C	30 W	Supply voltage, max	250 V
Supply voltage, min.	110 V	Type of connection	Pre-assembled cable
Type of mounting	Rail	With room thermostat	No

Classifications

ETIM 6.0	EC000737	eClass 6.2	27-18-07-16
eClass 9.1	27-18-07-10		

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	STEP
User Documentation	Operating instructions