



PIN OUT

A1	——	A1	B1	——	B1
A2	——	A2	B2	——	B2
A3	——	A3	B3	——	B3
A4	——	A4	B4	——	B4
A5	——	A5	B5	——	B5
A6	——	A6	B6	——	B6
A7	——	A7	B7	——	B7
A8	——	A8	B8	——	B8
A9	——	A9	B9	——	B9
A10	——	A10	B10	——	B10
A11	——	A11	B11	——	B11
A12	——	A12	B12	——	B12

NOTES:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10MΩ Min;
 - Contact resistance:3Ω Max;
 Data Transfer: 10Gbps Voltages:5V Current:3A, RoHS 2.0 and REACH Compliant
- ENVIRONMENTAL:
 - Operation temperature :-10℃~+60℃
 - Storage temperature :-20℃+75℃
 - Operation humidity :10%~85%
 - Storage humidity :10%~85%

ITEM NO. :	Color
255332S	Black
255332	White

MATERIAL LIST:

②	Housing	ABS	1	
①	Connector	USB C Female,Black insulation The Pin Gold Plating, the Shell For Nickel plating	2	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

CUSTOMER	CN	ITEM NO.	
PRODUCT NAME	USB 3.1 GEN2 Type C male to C Female Adapter keystone Type	UNO ITEM NO.	UNIT MM
DRAWNBY		APPOBY	DATE
wbs	Alvan		2018-08-28

NEW			2018-08-28	A
REVISION RECORD MODIFICATIONS			DATE	REV.