



VGA Splitter Pro, 450MHz, 2 Port

Part No.: 32571

Description

- Duplicates the video signal from your PC to 2 CRT or LCD monitors
- Provides a simultaneous display on all connected monitors
- Enhances video signals for long distance broadcasting (up to 55m)
- Maximum Resolution: 2048 x 1536
- Power supply included
- 3 Year Warranty

This compact video splitter is a very effective solution for users who need to distribute multiple video signals over long distances. It supports high resolution VGA signals of up to 2048 x 1536 (QXGA) and, when using LINDY Premium Gold cables, distances of up to 55m.

Typical applications include:

- School/College/University Training - enables tutor to work from their local monitor and split the video output to a large screen video projector
- Shops, Supermarkets, Pubs, Restaurants, Hotels - advertise products on several displays throughout the building
- Computer Supplies - demonstrate four monitors using only one PC
- Monitor Testing/Repair - four monitors can be tested using only one PC

Please note: VGA cables are not included. For best results, we recommend you use LINDY Premium Gold cables.

A 4 Port VGA Splitter Pro and a 8 Port VGA Splitter Pro are also available.

Technical details

Additional information:

- Can be used with CRT and LCD/TFT displays
- High Bandwidth: 450MHz for each port
- Cascadable- several units may be daisy chained for additional displays
- Connectors: 15 Way HD Male (input) and 15 Way HD Female (output)
- Dimensions: 130 x 80 x 45mm (WxDxH)

© LINDY 2019