



1m DVI-D Dual Link Cable, Gold Line

Part No.: 36201

Description

- No compromise DVI-D Dual Link cable for demanding environments and mission critical systems
- Supports DVI resolutions up to 2560x1600@60Hz and HD resolutions up to 1080p
- Full metal 24K gold plated housing, 24K gold plated connectors and contacts
- Low attenuation triple shielded cable, corrosion resistant, high performance OFC 28AWG conductors
- 25 year warranty

From the Lines cable connectivity concept by Lindy, Gold Line DVI-D Dual Link cables are the no compromise, high resolution connection solution for use in the most demanding professional environments.

Gold Line DVI-D Dual Link cables feature triple shielded construction with 28AWG OFC conductors for premium performance and corrosion resistance. High quality 24K gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

The full metal housing incorporates an integrated finger grip for easy installation. Large thumb screws allow the connector to be tightened into place without the need for a screwdriver and a flexible strain relief prolongs cable life.

These superior quality cables utilise a unique low attenuation design that ensures consistent and reliable transmission even over very long distances.

Gold Line DVI-D Dual Link cables support DVI resolutions up to 2560x1600@60Hz including HD resolutions up to 1080p.

Gold DVI-D Dual Link cables are available in lengths: 0.5m, 1, 2m, 3m,5m, 7.5m, 10m, 15m, 20m and 25m

Technical details

Connectors

- Connector A: DVI-D Male (Dual Link)
- Connector B: DVI-D Male (Dual Link)
- Housing Material: 24K Gold Plated Metal
- Connector Plating: 24K Gold 3µm
- Pin Construction: Phosphor Bronze
- Pin Plating: 24K Gold 15µm
- Dimensions (approx.) WxDxH: 39.5x44.5x16.5mm (1.55x1.73x0.65in)

Cable Construction

- Length: 1m (3.28ft)
- Standard: DVI-D Dual Link
- Colour: Grey
- Type: Round
- Jack Diameter: 8.6mm (0.34in)
- Jacket Material: PVC
- Conductor Material: OFC Copper
- Conductor Gauge: 28AWG
- Shielding: Copper Braid 85%

Specifications

- Supported Bandwidth: 9.9 Gbps
- Maximum Resolution: 2560x1600@60Hz
- Nominal Attenuation: 1 - 825Mhz < 8db
- Minimum Bend Radius: 120mm (4.72in)
- Operating Temperature: -20°C - 80°C (-4°F - 176°F)
- Storage Temperature: -25°C - 85°C (-13°F - 185°F)

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 25
- Certificated: RoHS, REACH, UL

Purchasing Information

- No. 36201
- EAN: 4002888362016

This product is also available in other lengths

- 36200 - 0.5m (1.64ft)
- 36202 - 2m (6.56ft)
- 36203 - 3m (9.84ft)
- 36204 - 5m (16.40ft)
- 36205 - 7.5m (24.61ft)
- 36206 - 10m (32.81f)

© LINDY 2019