



## 0.5m HDMI to DVI-D Cable, Gold Line

Part No.: 36193

### Description

- No compromise, ultimate performance HDMI to DVI-D cable for demanding environments and mission critical systems
- Supports DVI resolutions up to 1920x1200@60Hz and HDTV resolutions up to 1080p
- Full metal 24K gold plated housing, 24K gold plated connectors and contacts
- Low attenuation triple shielded cable, corrosion resistant, high performance OFC 24AWG conductors
- 25 year warranty

From the Lines cable connectivity concept developed by Lindy, Gold Line HDMI to DVI-D cables are the no compromise, high performance connection solution for use in the most demanding professional environments.

Gold Line HDMI to DVI-D cables feature triple shielded construction with 24AWG OFC conductors for premium performance and corrosion resistance. High quality 24K gold plated contracts and connectors maintain optimal signal integrity and maximum reliability.

Gold Line HDMI to DVI-D cables support DVI resolutions up to 1920x1200@60Hz including HD resolutions up to 1080p.

These superior quality cables utilise a unique low attenuation design that ensures consistent and reliable transmission even over very long distances.

Gold Line HDMI to DVI-D cables are available in lengths: 0.5m, 1m, 2m, 3m, 5m, 10m and 15m

## Technical details

### Connectors

- Connector A: HDMI Typ A Male
- Connector B: DVI-D Male (Single Link)
- Housing Material: 24K Gold Plated Metal
- Connector Plating: 24K Gold 3µm
- Pin Construction: Phosphor Bronze
- Pin Plating: 24K Gold 15µm
- Dimensions (approx.) WxDxH:
  - HDMI: 20x36x11.2mm (0.78x1.42x0.44in)
  - DVI: 39.5x44.5x16.5mm (1.55x1.73x0.65in)

### Cable Construction

- Length: 0.5m (1.64ft)
- Standard: DVI-D Single Link
- Colour: Grey
- Type: Round
- Jack Diameter: 9mm (0.35in)
- Jacket Material: PVC
- Conductor Material: OFC Copper
- Conductor Gauge: 24AWG
- Shielding: Copper Braid 85%

### Specifications

- Supported Bandwidth: 4.95 Gbps
- Maximum Resolution: 1920x1200@60Hz
- Nominal Attenuation: 1 - 825Mhz < 8db
- Minimum Bend Radius: 126mm (4.96in)
- Operating Temperature: -20°C - 80°C (-4°F - 176°F)
- Storage Temperature: -25°C - 85°C (-13°F - 185°F)

### Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 25
- Certificated: RoHS, REACH, UL

### Purchasing Information

- No. 36193

- EAN: 4002888361934

This product is also available in other lengths

- 36194 - 1m (3.28ft)
- 36195 - 2m (6.56ft)
- 36196 - 3m (9.84ft)
- 36197 - 5m (16.40ft)
- 36198 - 10m (32.81ft)
- 36199 - 15m (49.21ft)

© LINDY 2019