



5m DVI-D Dual Link Cable, Anthra Line

Part No.: 36224

Description

- Professional choice DVI-D Dual Link cable for commercial and high performance AV and IT installations
- Supports DVI resolutions up to 2560x1600 @60Hz and HDTV resolutions up to 1080p
- Robust PVC housing, 24K gold plated connectors and contacts
- Triple shielded cable, corrosion resistant tinned copper 28AWG conductors
- 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Anthra Line DVI-D Dual Link cables are the professional choice for high resolution connections in commercial AV and IT applications.

Anthra Line DVI-D Dual Link are premium cables that feature triple shielded construction with 28AWG tinned copper conductors for performance and corrosion resistance. High quality 24K gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

The tough PVC housing incorporates an integrated finger grip for easy installation. Large thumb screws allow the connector to be tightened into place without the need for a screwdriver and a flexible strain relief prolongs cable life.

Anthra Line DVI-D Dual Link cables support resolutions up to 2560x1600@60Hz including HDTV resolutions up to 1080p.

Anthra Line DVI-D Dual Link cables are available in lengths of 0.5m, 1m, 2m, 3m, 5m, 7.5m, 10m, 15m and 20m

Technical details

Connectors

- Connector A: DVI-D Male (Dual Link)
- Connector B: DVI-D Male (Dual Link)
- Housing Material: PVC
- Connector Plating: 24K Gold 1µm
- Pin Construction: Brass
- Pin Plating: 24K Gold 1µm
- Dimensions (approx.) WxDxH: 39.5x16.5x44.5mm (1.56x0.65x1.75in)

Cable Construction

- Length: 5m (16.40ft)
- Standard: DVI-D Dual Link
- Colour: Black
- Type: Round
- Jack Diameter: 8.6mm (0.34in)
- Jacket Material: PVC
- Conductor Material: Bare Copper
- Conductor Gauge: 28AWG
- Shielding: Aluminium Magnesium Braid 75%

Specifications

- Supported Bandwidth: 9.9 Gbps
- Maximum Resolution: 2560x1600@60Hz
- Nominal Attenuation: 1 - 825Mhz < 8db
- Minimum Bend Radius: 86mm (3.39in)
- Operating Temperature: -20°C - 80°C (-4°F - 176°F)
- Storage Temperature: -25°C - 85°C (-13°F - 185°F)

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH, UL

Purchasing Information

- No. 36224
- EAN: 4002888362245

This product is also available in other lengths

- 36220 - 0.5m (1.64ft)
- 36221 - 1m (3.28ft)
- 36222 - 2m (6.56ft)
- 36223 - 3m (9.84ft)
- 36225 - 7.5m (24.61ft)
- 36226 - 10m (32.81ft)
- 36227 - 15m (49.21ft)
- 36228 - 20m (65.62ft)

© LINDY 2019