



10m Standard HDMI Cable, Gold Line

Part No.: 37866

Description

- No compromise, ultimate performance Standard HDMI 2.0 cable for demanding environments and mission critical systems
- Supports UHD resolutions up to 4096x2160@60Hz 4:2:0 8bit
- Full metal 24K gold plated housing, 24K gold plated connectors and contacts
- Low attenuation triple shielded cable, corrosion resistant, high performance OFC 24AWG conductors
- HDMI 2.0 compliant: 3D, 4K, 10.2Gbps, HEC, ARC, CEC, Dolby True HD, DTS-HD Master Audio; HDMI ATC certified; 25 year warranty

From the Lines cable connectivity concept developed by Lindy, Gold Line Standard HDMI cables are the no compromise, high performance connection solution for use in the most demanding professional environments.

Gold Line Standard HDMI cables feature triple shielded construction with 24AWG OFC conductors for premium performance and corrosion resistance. High quality 24K gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

UHD resolutions up to 4K 4096x2160@60Hz 4:2:0 8bit are supported. Gold Line HDMI cables are also capable of transmitting 32 channel audio and Dolby True HD.

These superior quality cables utilise a unique low attenuation design that ensures consistent and reliable transmission even over very long distances.

The HDMI 2.0 specification is supported for 10.2Gbps bandwidth capacity in cable lengths above

7.5m. Gold Line HDMI cables are classified as High Speed up to 7.5m and Standard at lengths above 7.5m

Gold Line HDMI cables are available in lengths: 0.5m, 1m, 2m, 3m, 5m, 7.5m, 10m, 15m and 20m

Technical details

Connectors

- Connector A: HDMI Type A Male
- Connector B: HDMI Type A Male
- Housing Material: 24K Gold Plated Zinc Alloy
- Connector Plating: 24K Gold 3µm
- Pin Construction: Phosphor Bronze
- Pin Plating: 24K Gold 15µm
- Dimensions (approx.) WxDxH: 20x11.6x34.1mm (0.79x0.46x1.34in)

Cable Construction

- Length: 10m (32.81ft)
- Standard: Standard HDMI with Ethernet
- Colour: Grey
- Type: Round
- Jack Diameter: 8.5mm (0.33in)
- Jacket Material: PVC
- Conductor Material: OFC Copper
- Conductor Gauge: 24AWG
- Shielding: Copper Braid 85%

Specifications

- Supported Bandwidth: 10.2Gbps
- Maximum Resolution: 4096x2160@60Hz 4:2:0 8bit
- Nominal Attenuation: 300kHz-825MHz <5dB, 825MHz-2.475GHz <5dB, 2.475GHz-4.125GHz <12dB, 4.125GHz-5.1GHz <20dB
- Minimum Bend Radius: 85mm (3.35in)
- Operating Temperature: -10°C - 80°C (14°F - 176°F)
- Storage Temperature: -10°C - 80°C (14°F - 176°F)
- ATC Approved: Yes

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 25

- Certificated: RoHS, REACH, UL, ATC

Purchasing Information

- No. 37866
- EAN: 4002888378666

This product is also available in other lengths

- 37860 - 0.5m (1.64ft)
- 37861 - 1m (3.28ft)
- 37862 - 2m (6.56ft)
- 37863 - 3m (9.84ft)
- 37864 - 5m (16.44ft)
- 37865 - 7.5m (24.61ft)
- 37867 - 15m (49.21ft)
- 37868 - 20m (65.62ft)

© LINDY 2019