



## 1m High Speed HDMI Cable, Cromo Line

Part No.: 37871

### Description

- Superior performance and design High Speed HDMI 2.0 cable
- Supports UHD resolutions up to 4096x2160@60Hz 4:4:4 8bit
- Chrome design ABS housing, 24K gold plated connectors and contacts
- Triple shielded cable, corrosion resistant, high performance tinned copper 30 AWG conductors
- HDMI 2.0 compliant: 3D, 4K, 18Gbps, HEC, ARC, CEC, Dolby True HD, DTS-HD Master Audio; HDMI ATC certified; 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Cromo Line High Speed HDMI cables are high performance, designer connections that combine premium construction materials with striking connector architecture.

Cromo Line High Speed HDMI cables feature triple shielded construction with 30AWG tinned copper conductors for premium performance and corrosion resistance. High quality 24K gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

UHD resolutions up to 4K 4096x2160@60Hz 4:4:4 8bit are supported. Cromo Line HDMI cables are also capable of transmitting 32 channel audio and Dolby True HD.

Cromo Line cables feature sleek chrome design ABS housing to complement the aesthetics of style focused commercial and home applications.

The HDMI 2.0 specification is supported for 18Gbps bandwidth capacity in cable lengths up to 5m. Any cables below 5m are classified as high speed, any lengths above 5m are standard cables.

Cromo Line HDMI cables are available in lengths: 0.3m, 0.5m, 1m, 2m, 3m, 5m, 7.5m and 10m

## Technical details

### Connectors

- Connector A: HDMI Type A Male
- Connector B: HDMI Type A Male
- Housing Material: Chrome Plated ABS Plastic
- Connector Plating: 24K Gold 3µm
- Pin Construction: Phosphor Copper
- Pin Plating: 24K Gold 15µm
- Dimensions (approx.) WxDxH: 20x34.1x11.8mm (0.79x1.34x0.47in)

### Cable Construction

- Length: 1m (3.28ft)
- Standard: High Speed HDMI with Ethernet
- Colour: Grey
- Type: Round
- Jack Diameter: 6mm (0.24in)
- Jacket Material: PVC
- Conductor Material: Tin plated copper
- Conductor Gauge: 30AWG
- Shielding: Copper Braid 85%

### Specifications

- Supported Bandwidth: 18Gbps
- Maximum Resolution: 4096x2160@60Hz 4:4:4 8bit
- Nominal Attenuation: 300kHz-825MHz <5dB, 825MHz-2.475GHz <5dB, 2.475GHz-4.125GHz <12dB, 4.125GHz-5.1GHz <20dB
- Minimum Bend Radius: 60mm (2.36in)
- Operating Temperature: -10°C - 80°C (14°F - 176°F)
- Storage Temperature: -10°C - 80°C (14°F - 176°F)
- ATC Approved: Yes

### Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH, UL, ATC

### Purchasing Information

- No. 37871
- EAN: 4002888378710

This product is also available in other lengths

- 37869 - 0.3m (0.98ft)
- 37870 - 0.5m (1.64ft)
- 37872 - 2m (6.56ft)
- 37873 - 3m (9.84ft)
- 37874 - 5m (16.44ft)
- 37875 - 7.5m (24.61ft)
- 37876 - 10m (32.81ft)

© LINDY 2019