



## 5m High Speed HDMI Cable, Gold Line

Part No.: 37864

### Description

- Advanced, high performance HDMI cable with slimline metal connectors
- Supports UHD resolutions up to 4096x2160@60Hz 4:4:4 8bit
- Supports Dolby® True HD, DTS-HD Master Audio up to 32 audio channels
- Full support for HEC, ARC and CEC compliant devices
- 25 year warranty

From the Lines cable connectivity concept developed by Lindy, Gold Line High Speed HDMI cables are the no compromise, high performance connection solution for use in the most demanding professional environments.

These superior quality cables utilise a unique low attenuation design that ensures consistent and reliable transmission even over very long distances.

For complete signal integrity, Gold Line HDMI cables feature 24K gold plated contacts, triple shielding with 100% aluminium mylar wrap and an 85% tinned copper braid.

UHD resolutions up to 4K 4096x2160@60Hz 4:4:4 8bit are supported. Gold Line HDMI cables are also capable of transmitting 32 channel audio and Dolby® True HD.

The latest HDMI specifications are supported for 18G bandwidth capacity in cable lengths up to 7.5m. Gold Line HDMI cables are classified as High Speed up to 7.5m and Standard at lengths above 7.5m

Gold Line HDMI cables are available in lengths of 0.5m, 1m, 2m, 3m, 5m, 7.5m, 10m, 15m and 20m

## Technical details

### Connectors

- Connector A: HDMI Type A Male
- Connector B: HDMI Type A Male
- Housing Material: 24K Gold Plated Zinc Alloy
- Connector Plating: 24K Gold 3µm
- Pin Construction: Phosphor Bronze
- Pin Plating: 24K Gold 15µm
- Dimensions (approx.) WxDxH: 20x11.6x34.1mm (0.79x0.46x1.34in)

### Cable Construction

- Length: 5m (16.4ft)
- Standard: High Speed HDMI with Ethernet
- Colour: Grey
- Type: Round
- Jack Diameter: 8.5mm (0.33in)
- Jacket Material: PVC
- Conductor Material: OFC Copper
- Conductor Gauge: 24AWG
- Shielding: Copper Braid 85%

### Specifications

- Supported Bandwidth: 18Gbps
- Maximum Resolution: 4096x2160@60Hz 4:4:4 8bit
- Nominal Attenuation: 300kHz-825MHz <5dB, 825MHz-2.475GHz <5dB, 2.475GHz-4.125GHz <12dB, 4.125GHz-5.1GHz <20dB
- Minimum Bend Radius: 85mm (3.35in)
- Operating Temperature: -10°C - 80°C (14°F - 176°F)
- Storage Temperature: -10°C - 80°C (14°F - 176°F)
- ATC Approved: Yes

### Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 25
- Certificated: RoHS, REACH, UL, ATC

## Purchasing Information

- No. 37864
- EAN: 4002888378642

This product is also available in other lengths

- 37860 - 0.5m (1.64ft)
- 37861 - 1m (3.28ft)
- 37862 - 2m (6.56ft)
- 37863 - 3m (9.84ft)
- 37865 - 7.5m (24.61ft)
- 37866 - 10m (32.81ft)
- 37867 - 15m (49.21ft)
- 37868 - 20m (65.62ft)

© LINDY 2019