



IEC C19 to C20 Extension Cable, Blue, 2m

Part No.: 30121

Description

- Ideal for use with UPSs, servers, remote power switches etc.
- IEC C19 to IEC C20 connectors
- Rated at 16 Amps
- Fully moulded
- 10 year warranty

Lindy C19 to C20 extension cables are rated at 16 amps / 250V which make them ideal for use with heavy duty UPS devices. These cables are available in 3 colours, Blue, Red and Orange. This allows you to colour code your heavy duty devices in your server room.

Package Contents:

2m IEC C19 to C20 Extension Cable, Blue

Technical details

- Connector A: IEC C19
- Connector B: IEC C20
- Cable Type: H05-VVF 3G * 1.50mm²
- Number of cores: 3
- Wire cross section: 1.50mm²
- Available lengths: 1m - 3m
- Operating temperature: approx. -10 to 70 ° C
- Storage temperature: approx. -25 to 70 ° C
- Colour: Blue

- 10 year warranty

© LINDY 2019