



**7.5m USB 2.0 Type A to B Cable, Anthra Line**  
Part No.: 36676

## Description

- Professional choice USB 2.0 Type A to B cable for commercial and high performance AV and IT installations
- Supports data transfer speeds up to 480Mbps
- Robust PVC housing, nickel connectors and gold plated contacts
- Double shielded cable, corrosion resistant tinned copper conductors
- USB 2.0, 480Mbps
- 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Anthra Line USB 2.0 Type A to B cables are the professional choice for high performance connections in commercial AV and IT installations.

Anthra Line USB 2.0 cables are premium connections that feature double shielded construction with copper conductors for performance and corrosion resistance. High quality gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

Data transfer speeds up to 480Mbps are supported for the quick and effortless transfer of large data volumes.

Anthra Line USB 2.0 Type A to B cables are available in lengths from 0.2m to 10m.

## Technical details

## Connectors

- Connector A: USB 2.0 Type A Male
- Connector B: USB 2.0 Type B Male
- Housing Material: PVC
- Connector Plating: Nickel
- Pin Construction: Copper
- Pin Plating: Gold
- Dimensions (approx.) WxDxH:
  - A: 15.5x35x7.8mm (0.61x1.38x0.31in)
  - B: 11.8x35x10.2mm (0.47x1.38x0.40in)

## Cable Construction

- Length: 7.5m (24.61ft)
- Standard: USB 2.0
- Colour: Black
- Type: Round
- Jacket Diameter: 4.4mm (0.17in)
- Jacket Material: PVC
- Conductor Material: Tinned Copper
- Conductor Gauge: 26/28AWG
- Shielding: Aluminium Magnesium Braid

## Specifications

- Supported Bandwidth: 480Mbps
- Maximum Resolution: -
- Nominal Attenuation: 5.8db/km
- Minimum Band Radius: 16mm (0.63in)
- Operating Temperature: 0°C - 60°C (32°F - 140°F)
- Storage Temperature: 0°C - 60°C (32°F - 140°F)
- ATC Approved: -

## Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH & UL

## Purchasing Information

- No.: 36676
- EAN: 4002888366762

This product is also available in other lengths

- 36670 - 0.2m (0.66ft)
- 36671 - 0.5m (1.64ft)
- 36672 - 1m (3.28ft)
- 36673 - 2m (6.56ft)
- 36674 - 3m (9.84ft)
- 36675 - 5m (16.44ft)
- 36676 - 7.5m (24.61ft)
- 36677 - 10m (32.81ft)

© LINDY 2019