



0.5m USB 2.0 Type A Extension Cable, Anthra Line

Part No.: 36701

Description

- Professional choice USB 2.0 Type A Extension cable for commercial and high performance AV and IT installations
- Supports data transfer speeds up to 480Mbps
- Robust PVC housing, nickel connectors and gold plated contacts
- Double shielded cable, corrosion resistant tinned copper conductors
- USB 2.0, 480Mbps; 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Anthra Line USB 2.0 Type A Extension cables are the professional choice for high performance connections in commercial AV and IT installations.

Anthra Line USB 2.0 cables are premium connections that feature double shielded construction with copper conductors for performance and corrosion resistance. High quality gold plated contacts and nickel connectors maintain optimal signal integrity and maximum reliability.

Data transfer speeds up to 480Mbps are supported for the quick and effortless transfer of large data volumes.

Anthra Line USB 2.0 Type A Extension cables are available in lengths from 0.2m, 0.5m, 1m, 2m, 3m and 5m

Technical details

Connectors

- Connector A: USB 2.0 Type A Male
- Connector B: USB 2.0 Type A Female
- Housing Material: PVC
- Connector Plating: Nickel
- Pin Construction: Copper
- Pin Plating: Gold
- Dimensions (approx.) WxDxH:
 - A (M): 15.5x35x7.8mm (0.61x1.38x0.31in)
 - A (F): 17x35x9.8mm (0.67x1.38x0.39in)

Cable Construction

- Length: 0.5m (1.64ft)
- Standard: USB 2.0
- Colour: Black
- Type: Round
- Jacket Diameter: 4.4mm (0.17in)
- Jacket Material: PVC
- Conductor Material: Tinned Copper
- Conductor Gauge: 26/28AWG
- Shielding: Aluminium Magnesium Braid

Specifications

- Supported Bandwidth: 480Mbps
- Maximum Resolution: -
- Nominal Attenuation: 5.8db/km
- Minimum Band Radius: 16mm (0.63in)
- Operating Temperature: 0°C - 60°C (32°F - 140°F)
- Storage Temperature: 0°C - 60°C (32°F - 140°F)
- ATC Approved: -

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH & UL

Purchasing Information

- No.: 36701
- EAN: 4002888367011

This product is also available in other lengths

- 36700 - 0.2m (0.66ft)
- 36701 - 0.5m (1.64ft)

- 36702 - 1m (3.28ft)
- 36703 - 2m (6.56ft)
- 36704 - 3m (9.84ft)
- 36705 - 5m (16.44ft)

© LINDY 2019