



1m USB 3.0 Typ A to B Cable, Anthra Line

Part No.: 36741

Description

- Professional choice USB 3.0 Type A to B cable for commercial and high performance AV and IT installations
- Supports SuperSpeed data transfer speeds up to 5Gbps
- Robust PVC housing, gold plated connectors and contacts
- Triple shielded cable, corrosion resistant tinned copper conductors
- SuperSpeed, USB 3.0, 5Gbps; 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Anthra Line USB 3.0 Type A to B cables are the professional choice for high performance connections in commercial AV and IT installations.

Anthra Line USB 3.0 cables are premium connections that feature triple shielded construction with copper conductors for performance and corrosion resistance. High quality gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

The SuperSpeed protocol is supported with up to 5Gbps bandwidth to allow the rapid transfer of large data volumes.

Anthra Line USB 3.0 Type A to B cables are available in lengths from 0.5m, 1m, 2m, 3m and 5m

Technical details

Connectors

- Connector A: USB 3.0 Type A Male
- Connector B: USB 3.0 Type B Male
- Housing Material: PVC
- Connector Plating: Gold Plated
- Pin Construction: Copper
- Pin Plating: Gold Plated
- Dimensions (approx.) WxDxH:
 - A: 15.5x35x7.8mm (0.61x1.38x0.31in)
 - B: 12.2x35x13.5mm (0.48x1.38x0.53in)

Cable Construction

- Length: 1m (3.28ft)
- Standard: USB 3.0
- Colour: Black
- Type: Round
- Jacket Diameter: 5.5mm (0.22in)
- Jacket Material: PVC
- Conductor Material: Tinned Copper
- Conductor Gauge: 24/28/30AWG
- Shielding: Aluminium Braid 85%

Specifications

- Supported Bandwidth: 5Gbps
- Maximum Resolution: -
- Nominal Attenuation: 0.5MHz-7.5GHz<25DB
- Minimum Bend Radius: 48mm (1.89in)
- Operating Temperature: 0°C - 60°C (32°F - 140°F)
- Storage Temperature: 0°C - 60°C (32°F - 140°F)
- ATC Approved: -

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH & UL

Purchasing Information

- No.: 36741
- EAN: 4002888367417

This product is also available in other lengths

- 36740 - 0.5m (1.64ft)
- 36741 - 1m (3.28ft)

- 36742 - 2m (6.56ft)
- 36743 - 3m (9.84ft)
- 36744 - 5m (16.40f)

© LINDY 2019