



## External SSD Enclosure, M2 - USB 3.0



### Quick Installation Guide DA-71111 Rev. 2

#### Description

The aluminum enclosure enables the installation of a NGFF SSD which can be connected via USB to the PC or laptop.

#### Specification

- **Connector:**
  - External: 1 x Micro USB 3.0 Type-B female
  - Internal: 1 x NGFF 6 Gb/s slot
- **Chipset:** Asmedia ASM1153E
- Support UASP
- Support M.2 SATA SSD only, not support M.2 PCIE SSD
- Support SSD: 22x 30mm/42mm/60mm/80mm NGFF(M.2)
- Support Max. capacity of SSD to 2 TB
- Data transfer rate up to 5 Gb/s
- LED indicator for power and access
- **Color:** black
- Powered by USB3.0 cable, no extra power supply adapter needed
- Hot Plug, Plug & Play
- Assembled by screws

## System requirements

Windows Vista/7/8/8.1/10.

Mac OS 10.8

Linux Kernel 2.6

PC or laptop with a free USB Type-A port

## Package content

- External SSD Enclosure, M2 - USB 3.0
- Screwdriver, screws
- USB 3.0 Type-A to Micro USB cable (ca. 50 cm)



Hereby Assmann Electronic GmbH, declares that the Declaration of Conformity is part of the shipping content. If the Declaration of Conformity is missing, you can request it by post under the below mentioned manufacturer address.

[www.assmann.com](http://www.assmann.com)

Assmann Electronic GmbH

Auf dem Schüffel 3

58513 Lüdenscheid

Germany

