

BR1X / Ultra Compact PC kit

Dimension	46.8 mm x 112.6 mm x 119.4 mm (1.84" x 4.43" x 4.7")
Motherboard Size	105 x 110 mm
CPU	Intel® Pentium® Processor J5005 2.8GHz, 4 core (TDP 10W)
Memory	2 x SO-DIMM DDR4 slots 2400MHz Max. 8GB
LAN	Gigabit LAN (Realtek RTL8111HS)
Wifi Card	Intel® Dual Band Wireless-AC 3168
Graphics	Intel® UHD Graphics 605
Audio	Realtek ALC255
HDMI Resolution (Max.)	HDMI2.0a 4096 x 2160 @ 60 Hz
Mini DP Resolution (Max.)	DP1.2a 4096 x 2160 @ 60Hz
Expansion Slots	1 x M.2 slot (2280_storage) PCIe X2/SATA 1 x PCIe M.2 NGFF 2230 A-E key slot occupied by the WiFi+BT card
Front I/O	1 x USB3.0 1 x USB3.0 type C 1 x headphone jack with MIC
Rear I/O	1 x HDMI(2.0a) 1 x mini DisplayPort (1.2a) 2 x USB 3.0 1 x RJ45 1 x DC-In 1 x Kensington lock slot
Storage	Supports 2.5" HDD/SSD, 7.0/9.5 mm thick (1 x 6 Gbps SATA 3)
Power Supply	Input: AC 100-240V Output: DC 19V 2.1A
VESA	Bracket included Supports 75 x 75 and 100 x 100 mm
Support OS	WIN10 64bit
Environment	System Environment Operating Temperature: 0°C to +35°C System Storage Temperature: -20°C to +60°C