

Delock Cable DisplayPort 1.2 male > DisplayPort male 4K 1 m

Description

This cable enables you to connect DisplayPort devices e.g. a monitor to your PC. The DisplayPort is standardized universal connecting standard by VESA for the transfer of video and audiosignal. It can be applied for monitors, TV to computer, DVD-player and similar devices.



Specification

- Connector:
DisplayPort 20 pin male >
DisplayPort 20 pin male
- DisplayPort 1.2 specification
- 20 pin is connected (supports 3.3 V)
- Cable gauge:
30 AWG data line
28 AWG power line
- Cable diameter: ca. 6 mm
- Twisted-pair cabling
- Copper conductor
- Gold-plated connector
- Triple shielded cable
- Transfer of audio and video signals
- Data transfer rate up to 21.6 Gb/s
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Colour: black
- Length incl. connector: ca. 1 m

System requirements

- A free DisplayPort interface

Package content

- DisplayPort cable

Item no. 82423

EAN: 4043619824236

Country of origin: China

Package: Poly bag

Images



General	
Specification:	DisplayPort 1.2
Interface	
Connector 1:	1 x DisplayPort male
Connector 2:	1 x DisplayPort male
Technical characteristics	
Data transfer rate:	21,6 Gb/s
Maximum screen resolution:	3840 x 2160 @ 60 Hz
Physical characteristics	
Housing material:	PVC
Cable diameter:	6 mm
Connector finishing:	gold-plated
Pin finishing:	gold-plated
Conductor material:	copper
Conductor gauge:	30 AWG data line 28 AWG power line
Shielding:	triple
Length:	1 m
Colour:	black