

Technical Data

Material Polyamid 6.6

	PA66	W	HS	HIRHS
Raw material:	PA 66 standard	UV-resistant	Heat stabilised	Impact resistant / heat stabilised
Colour:	natural	Black	Natural or black	black
Working temperature:	-40°C to +85°C	-40°C to +85°C	-40°C to 105°C	-40°C to 105°C
short term (500 h):	+105°C	+105°C	+145°C	
density:	1,13 g/cm ³	1,13 g/cm ³	1,13 g/cm ³	1,10 g/cm ³
Melt point:	250-260 °C	250-260 °C	250-260 °C	262 °C
Flammability:	UL 94 V2	UL 94 V2	UL 94 V2	UL 94 HB
	halogenfree	halogenfree	halogenfree	