

LED floodlight PROFI 50W, neutral white

Product sheet

Basic Information

Order Number
Type
Common Number

850EMPR40WZS2640
ZS2640
ZS2640



8592920026298

Measuring Unit
Packaging
Net Weight [kg]
Dimensions [mm]

Pcs
1 / - / 4
2,65
265 × 145 × 295



Technical Description

source of light	LED
power	50 W
replacement of incandescent bulb	550 W
IP rating	IP65
luminous flux	5 000 lm
color temperature	4 000 K
light color	neutral white
color rendering index (CRI)	Ra >70

Product sheet

beam angle	120°
detection range of PIR Sensor	no PIR
dimensions	287 × 238 × 138 mm
colour	grey
voltage	100–240 V
current	220 mA
frequency	50/60 Hz
lifetime	40 000 hours
mechanical impact protection (IK)	IK08
warranty period	3 years
material of the diffuser	glass
body material	aluminum
working temperature range	-20 °C to +40 °C
line	PROFI
packaging	1 pc, box