

Product sheet

Basic Information

Order Number
Type
Common Number

850EMID40WZS2641
ZS2641
ZS2641



8592920039922



Measuring Unit
Packaging
Net Weight [kg]
Dimensions [mm]

Pcs
1 / - / 6
1,54
205 × 70 × 245



Technical Description

source of light	LED
power	50 W
replacement of incandescent bulb	430 W
IP rating	IP65
luminous flux	4 000 lm
color temperature	4 000 K
light color	neutral white
color rendering index (CRI)	Ra > 80

Product sheet

beam angle	120°
dimensions	230 × 45 × 197 mm
colour	grey
voltage	220–240 V~
current	210 mA
frequency	50/60 Hz
lifetime	25 000 hours
mechanical impact protection (IK)	IK08
warranty period	2 years
material of the diffuser	glass
body material	aluminum
working temperature range	-20 °C to +40 °C
line	IDEO
packaging	1 pc, box