

# LED floodlight PROFI 30W, neutral white

## Product sheet

### Basic Information

Order Number  
Type  
Common Number

**850EMPR30WZS2630**  
**ZS2630**  
**ZS2630**



8592920026274



Measuring Unit  
Packaging  
Net Weight [kg]  
Dimensions [mm]

Pcs  
1 / - / 6  
1,8  
210 × 120 × 235




### Technical Description

source of light	LED
power	30 W
replacement of incandescent bulb	350 W
IP rating	IP65
luminous flux	3 000 lm
color temperature	4 000 K
light color	neutral white
color rendering index (CRI)	Ra >70

## Product sheet

beam angle	120°
detection range of PIR Sensor	no PIR
dimensions	225 × 187 × 115 mm
colour	grey
voltage	100–240 V
current	128 mA
frequency	50/60 Hz
lifetime	40 000 hours
mechanical impact protection (IK)	IK08
warranty period	3 years
material of the diffuser	glass
body material	aluminum
working temperature range	-20 °C to +40 °C
line	PROFI
packaging	1 pc, box