

Product sheet

Basic Information

Order Number
Type
Common Number

850EMPRS30WZS2730
ZS2730
ZS2730



8592920026359

Measuring Unit
Packaging
Net Weight [kg]
Dimensions [mm]

Pcs
1 / - / 6
2,06
275 × 120 × 235



Technical Description

source of light	LED
power	30 W
replacement of incandescent bulb	350 W
IP rating	IP44
luminous flux	3 000 lm
color temperature	4 000 K
light color	neutral white
color rendering index (CRI)	Ra >70

Product sheet

beam angle	120°
PIR sensor	yes
detection range of PIR Sensor	12 m
dimensions	225 × 240 × 120 mm
colour	grey
voltage	100–240 V
current	128 mA
frequency	50/60 Hz
lifetime	40 000 hours
mechanical impact protection (IK)	IK08
warranty period	3 years
material of the diffuser	glass
body material	aluminum
working temperature range	-20 °C to +40 °C
line	PROFI
packaging	1 pc, box