

## Product sheet

### Basic Information

Order Number  
Type  
Common Number

**850EMIDS20WZS2721**  
**ZS2721**  
**ZS2721**



8592920039960

Measuring Unit  
Packaging  
Net Weight [kg]  
Dimensions [mm]

Pcs  
1 / - / 16  
0,711  
180 × 70 × 165



### Technical Description

source of light	LED
power	20 W
replacement of incandescent bulb	170 W
IP rating	IP54
luminous flux	1 600 lm
color temperature	4 000 K
light color	neutral white
color rendering index (CRI)	Ra > 80

## Product sheet

beam angle	120°
PIR sensor	yes
detection range of PIR Sensor	10 m
dimensions	158 × 56 × 166 mm
colour	grey
voltage	220–240 V~
current	175 mA
frequency	50/60 Hz
lifetime	25 000 hours
mechanical impact protection (IK)	IK08
warranty period	2 years
material of the diffuser	glass
body material	aluminum
working temperature range	-20 °C to +40 °C
line	IDEO
packaging	1 pc, box