

Product sheet

Basic Information

Order Number
Type
Common Number

850EMPRS20WZS2720
ZS2720
ZS2720



8592920026335



Measuring Unit
Packaging
Net Weight [kg]
Dimensions [mm]

Pcs
1 / - / 8
1,3
240 × 120 × 190



Technical Description

source of light	LED
power	20 W
replacement of incandescent bulb	200 W
IP rating	IP44
luminous flux	2 000 lm
color temperature	4 000 K
light color	neutral white
color rendering index (CRI)	Ra > 70

Product sheet

beam angle	120°
PIR sensor	yes
detection range of PIR Sensor	12 m
dimensions	180 × 210 × 120 mm
colour	grey
voltage	100–240 V
current	86 mA
frequency	50/60 Hz
lifetime	40 000 hours
mechanical impact protection (IK)	IK08
warranty period	3 years
material of the diffuser	glass
body material	aluminum
working temperature range	-20 °C to +40 °C
line	PROFI
packaging	1 pc, box