

## Product sheet

### Basic Information

Order Number  
Type  
Common Number

**850EMIDS40WZS2741**  
**ZS2741**  
**ZS2741**



8592920040003



Measuring Unit  
Packaging  
Net Weight [kg]  
Dimensions [mm]

Pcs  
1 / - / 6  
1,606  
275 × 74 × 250



### Technical Description

source of light	LED
power	50 W
replacement of incandescent bulb	430 W
IP rating	IP54
luminous flux	4 000 lm
color temperature	4 000 K
light color	neutral white
color rendering index (CRI)	Ra > 80

## Product sheet

beam angle	120°
PIR sensor	yes
detection range of PIR Sensor	10 m
dimensions	235 × 61 × 245 mm
colour	grey
voltage	220–240 V~
current	220 mA
frequency	50/60 Hz
lifetime	25 000 hours
mechanical impact protection (IK)	IK08
warranty period	2 years
material of the diffuser	glass
body material	aluminum
working temperature range	-20 °C to +40 °C
line	IDEO
packaging	1 pc, box