



Part No	90NB0IR1-M00730
Model Name	F540MA-GQ055T
EAN Code	4718017170017
UPC Code	192876170014
LCD Cover Color & Decoration	Chocolate Black IMR with Hairline
Top Case Color & Decoration	Gold IMR with Hairline
On board processor	Intel® Celeron® N4000 Processor (4M Cache, up to 2.6 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	15.6'//Ultra Slim 200nits//HD 1366x768 16:9//Anti-Glare//NTSC:45%
Chipset	N/A
Memory Slot	N/A
Total System Memory	LPDDR4 4GB
On board memory	LPDDR4 4GB
Memory Max.	4G
Storage	SATA 1TB 5400RPM 2.5' HDD
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	Intel UHD Graphics 600
Graphics Feature	N/A
Video memory	N/A
Video Camera	VGA Web Camera (Fixed type)
FingerPrint	N/A
On board Wireless	N/A
Wireless(Module)	802.11ac+Bluetooth 4.1 (Dual band) 1*1
LAN	N/A
Card Reader	Type: Micro SD
USB Port	2x USB 2.0 1x USB 3.0
Interface	1x Headphone-out & Audio-in Combo Jack 1x HDMI
Audio	Built-in speaker Built-in microphone Audio by ICEpower® Sonic Master
Weight (Kg)	1.84 KG (Without Battery) 2.00 KG (with 3 cell battery)
Dimension (cm)	38.1(W) x 25.2(D) x 2.72 ~ 2.72 (H) cm

AC Adapter	ø4.0 33W AC Adapter Output: 19V DC 1.75A, 33W , Input: 100-240V AC, 50/60 Hz universal
Battery	33WHrs, 3S1P, 3-cell Li-ion
Replaceable Battery	No
Keyboard type	Chiclet Keyboard
Keyboard Specification	ASUS 348mm keyboard with 19mm full size key pitch, integrated Numeric keypad
Software	ASUS Product Registration Program ASUS GiftBox ASUS Smart Gesture ASUS Splendid ASUS WebStorage Sync Agent Dropbox 25 GB Evernote ICESound KKBOX(JP/TW only) McAfee Internet Security(Trial version) Netflix (For specific region) WPS Office (NA, JP exclude)
Security	TPM (Firmware TPM) HDD User Password Protection and Security BIOS Booting User Password Protection
Supplied Accessories	Without carry bag
Warranty	1 year Carry-In Germany and Austria

