



3-in-1 4K Mini DisplayPort Adapter

Mini DisplayPort Male to HDMI/DVI/VGA Female, Active, White

Part No.: [207362](#)

Easily connect a Mini DisplayPort source with an HDMI, DVI or VGA display.

The Manhattan 3-in-1 4K Mini DisplayPort Adapter establishes a fast, simple and convenient link between a Mini DisplayPort source and a 4K HDMI or 1080p DVI and VGA displays. The adapter is easy and quick to install and requires no complicated configuration or setup. It offers an active connection for VGA and a passive connection for HDMI and DVI as well as a compact and integrated solution that eliminates unnecessary cables, tangles and clutter to keep installations and workspaces neat and orderly.

Features:

- 3-in-1 adapter converts a Mini DisplayPort signal to a 4K HDMI or 1080p DVI or VGA signal
- Delivers a high-quality digital video signal — ideal for using a Mini DP source with an HDMI, DVI or VGA display
- Supports Deep Color, high-bandwidth 3 Gbps applications and resolutions at 1080p (1920 x 1200p) for VGA and DVI or 4K (3840 x 2160p) for HDMI
- Allows monitor, TV or display to be configured in Extended or Mirrored modes
- HDMI configuration supports Ultra-High-Definition (UHD) video resolution up to 4K@30Hz (3840 x 2160p) and uncompressed digital 5.1 audio
- DVI configuration supports high definition video resolution up to 1080p@60Hz (1920 x 1080p); DVI does not support audio
- VGA configuration supports high-definition video resolution up to 1080p@60Hz (1920 x 1080p); VGA does not support audio
- Integrated design simplifies connections and eliminates cable tangles and clutter
- Three-year warranty

Specifications:

Standards and Certifications

- UL 20276
- DisplayPort v1.2
- FCC
- CE

Connections

- Mini DisplayPort 20-pin male
- HDMI 19-pin female, passive
- DVI 24+5-pin female, passive
- VGA/HD15 15-pin female, active
- Nickel-plated contacts
- Molded PVC and ABS Shell

General

- 8-bit and 10-bit Deep Color support
- 3 Gbps bandwidth
- Maximum single link resolution
3840 x 2160 (4K@30Hz) for HDMI
1920 x 1200 (1080p@60Hz) for DVI and VGA
- One-lane, one-direction, four-line connection support
- Active

Video Resolutions

- VGA: 640x480, 800x600, 1024x768, 1920x1200
- DTV/HDTV/UHDTV: 480i/480p/576i/576p/720p/1080i/1080p/4K@30Hz

Physical

- Cable length: 25 cm (10 in.)
- Housing: 7.5 x 4 x 1.8 cm (2.95 x 1.8 x 0.7 in.)
- Weight: 48 g (1.7 oz.)
- Housing: plastic

Operating Environment

- Operation Temperature: 0 – 40°C (32 – 104°F)
- Storage Temperature: -20 – 60°C (-4 – 140°F)
- Humidity (noncondensing): 0 – 80%

System Requirements

- Windows XP/Vista/7/8.1/10, Linux or Mac 9.x/10.x or above

Package Contents

- 3-in-1 4K Mini DisplayPort Adapter
- Quick Instruction Guide

