



1080p 2-Port HDMI Splitter

USB Powered, Black

Part No.: [207652](#)

Easily distribute a single HDMI signal to multiple displays.

The Manhattan 1080p 2-Port HDMI Splitter sends HDMI signals from a single Blu-ray player, satellite receiver, digital recorder, set-top box, game console or other HDMI source to two HDMI displays.

Flexible Solution for Many A/V Applications

Ideal for trade shows, classrooms, video conferencing, presentations and retail applications, the Manhattan 1080p 2-Port HDMI Splitter features a built-in booster for added signal strength. It's also a good choice for splitting and distributing a synchronous signal to multiple HDMI displays when source equipment is remotely stored in a secured room or cabinet. Users can cascade multiple units up to three levels and output HDMI video/audio to additional displays in widely distributed applications.

Quality Construction and Easy Installation

Full compliance with HDMI, HDCP 1.0, 1.1 and 1.2 as well as DVI 1.0 ensures that the Manhattan 1080p 2-Port HDMI Splitter can provide long service and reliable performance. Quickly connect HDMI cables (not included) and the USB power cable, and this affordable HDMI solution is complete — no complicated settings or software or hardware configurations necessary.

Features:

- Displays video from one HDMI source on two HD displays
- Delivers a sharp, clear signal from Blu-ray players, set-top boxes, satellite receivers and more
- Cascadable up to three levels to expand signal distribution to more displays
- HDCP compliant
- Supports LPCM, DTS@ Digital, DTS-HD Master Audio and Dolby TrueHD audio
- Supports 1080p HD resolution, 3D video and Deep Color
- Supports the video amplifier bandwidth up to 2.25 Gbps
- Plug and play
- Plug-and-play installation; no special setup or remote
- Gold-plated contacts

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Gold-plated contacts for corrosion-free connections
- Three-year warranty

Specifications:

Standards and Certifications

- HDCP 1.0 / 1.1 / 1.2
- DVI 1.0
- CE
- FCC
- RoHS2

General

- Source-to-splitter range: up to 15 m (49 ft.)
- Splitter-to-display range: up to 15 m (49 ft.)
- Power: 5 W; USB cable, 0.7 m (2.3 ft.)

Connections

- One HDMI female, 19-pin (input)
- Two HDMI female, 19-pin (output)
- One USB Mini-B female, 5-pin (input)

Signal Input/Output

- Input video signal: 0.5 – 1.0 V p-p
- Input DDC signal: 5 V p-p (TTL)
- Maximum single-link range: 2.25 Gbps, 1920x1200, 1080p
- Output video: HDMI 1.3b, HDCP 1.0 / 1.1 / 1.2, DVI 1.0
- Frequency: 2.25 Gbps / 225 MHz

Video Resolutions

- DTV/HDTV: 480i/480p/576i/576p/720p/1080i/1080p

Physical

- LED indicators: power and port connection
- On/off switch
- Dimensions: 60 x 54 x 20 mm (2.4 x 2.1 x 0.8 in.)
- Weight: 0.04 g (0.08 lb.)
- Housing: plastic

Operating Environment

- Operation Temperature: 0 – 70°C (32 – 158°F)
- Storage Temperature: -10 – 80°C (14 – 176°F)
- Operation Humidity (noncondensing): 10 – 85%
- Storage Humidity (noncondensing): 5 – 90%

Package Contents

- 1080p 2-Port HDMI Splitter

- USB power cable
- Quick Instruction Guide

