

**Industrial Ethernet
IE-FM5Z2LO0010MST0ST0-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Assembled IE cables, FO

General ordering data

Type	IE-FM5Z2LO0010MST0ST0-X
Order No.	1433990100
Version	Patch cable, ST IP 20, ST IP 20, 50 µm, LSZH, 10 m
GTIN (EAN)	4050118242775
Qty.	1 pc(s).

Industrial Ethernet

IE-FM5Z2L00010MST0ST0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	10 m	Length (inches)	0.394 inch
Net weight	158 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-20 °C
Operating temperature	-20 °C...70 °C	Storage temperature	
Installation temperature			

Standards

Connector standard	IEC 60874-10
--------------------	--------------

Fibre-optic

Attenuation	≤2.5 dB/km at 850 nm, ≤ 0.7 dB/km at 1300 nm	Bandwidth	≥ 500 MHz*km at 850 nm, ≥ 500 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM2		

Cable structure

Core diameter	50 µm	Sheath diameter	2.8 * 5.7 mm
Cable layout	ZIPCORD	Standard designations	I-V(ZN)H
Material sheath	LSZH	Sheathing colour	orange

Mechanical and material properties of cable

Min. bending radius, once only	28 mm	Min. bending radius, repetitive	56 mm
Halogen	No		

plug

Connector left	ST IP 20	Connector right	ST IP 20
----------------	----------	-----------------	----------

Classifications

ETIM 5.0	EC000034	ETIM 6.0	EC002607
eClass 6.2	27-06-18-03	eClass 7.1	27-06-18-03
eClass 8.1	27-06-18-03	eClass 9.0	27-06-10-03
eClass 9.1	27-06-10-03		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet IE-FM5Z2LO0010MST0ST0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Detailed drawing

