

**Automation Products - u-remote IP20
UR20-BM-SP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Similar to illustration**More performance. Simplified.
u-remote.**

Weidmüller u-remote – our innovative remote I/O concept with IP 20 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, no more downtime. For considerably improved performance and greater productivity.

Reduce the size of your cabinets with u-remote, thanks to the narrowest modular design on the market and the need for fewer power-feed modules. Our u-remote technology also offers tool-free assembly, while the modular "sandwich" design and integrated web server speed up installation, both in the cabinet and machine. Status LEDs on the channel and each u-remote module enable reliable diagnosis and rapid service.

This and many other amazing ideas boost the availability of your machines and systems. And ensure smooth processes too. From planning to operation.

u-remote stands for "More Performance". Simplified

General ordering data

Type	UR20-BM-SP
Order No.	1350930000
Version	Replacement part, , Flange-mounted housing
GTIN (EAN)	4050118402735
Packaging	Cardboard box

Automation Products - u-remote IP20 UR20-BM-SP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	11.5 mm	Width (inches)	0.453 inch
Height	128 mm	Height (inches)	5.039 inch
Depth	58 mm	Depth (inches)	2.283 inch
Net weight	29.9 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

ETIM 5.0	EC002584	ETIM 6.0	EC002584
eClass 6.2	27-24-26-92	eClass 7.1	27-24-26-91
eClass 8.1	27-24-26-91	eClass 9.0	27-33-02-92
eClass 9.1	27-24-26-90		

Approvals

ROHS	Conform
------	---------