

Automation Products - u-remote IP20 UR20-BM-PF-O-SIL-SP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Similar to illustration



More performance. Simplified. u-remote.

Weidmüller u-remote – our innovative remote I/O concept with IP 20 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, no more downtime. For considerably improved performance and greater productivity.

Reduce the size of your cabinets with u-remote, thanks to the narrowest modular design on the market and the need for fewer power-feed modules. Our u-remote technology also offers tool-free assembly, while the modular "sandwich" design and integrated web server speed up installation, both in the cabinet and machine. Status LEDs on the channel and each u-remote module enable reliable diagnosis and rapid service.

This and many other amazing ideas boost the availability of your machines and systems. And ensure smooth processes too. From planning to operation.

u-remote stands for "More Performance". Simplified

General ordering data

| | |
|------------|--|
| Type | UR20-BM-PF-O-SIL-SP |
| Order No. | 1350970000 |
| Version | Replacement part, , Flange-mounted housing |
| GTIN (EAN) | 4050118398342 |
| Packaging | Cardboard box |

Automation Products - u-remote IP20 UR20-BM-PF-O-SIL-SP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 11.5 mm | Width (inches) | 0.453 inch |
| Height | 128 mm | Height (inches) | 5.039 inch |
| Depth | 58 mm | Depth (inches) | 2.283 inch |
| Net weight | 29.9 g | | |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 5.0 | EC002584 | ETIM 6.0 | EC002584 |
| eClass 6.2 | 27-24-26-92 | eClass 7.1 | 27-24-26-91 |
| eClass 8.1 | 27-24-26-91 | eClass 9.0 | 27-33-02-92 |
| eClass 9.1 | 27-24-26-90 | | |

Approvals

ROHS Conform

Downloads

Brochure/Catalogue [CAT U_REMOTE 16/17 EN](#)