Industrial Ethernet
IE-CSPS5VS0010VAPVAP-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Assembled IE cables, PROFINET, with push-pull power plug connector according to PROFINET specifications

General ordering data

Type	IE-CSPS5VS0010VAPVAP-X
Order No.	1350120010
Version	System cable, PushPull Power, PushPull Power, PVC, 1 m
GTIN (EAN)	4050118165296
Qty.	1 pc(s).

Industrial Ethernet
IE-CSPS5VS0010VAPVAP-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	1 m	Length (inches)	0.039 inch
Net weight	306 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Electrical properties

Current-carrying capacity at 50 °C	16 A	Rated voltage	24 V

Standards

Connector standard	in accordance with PROFINET specification

Cable structure

Wire connection cross section AWG, max.	AWG 16	Cross-section	5*1.5 mm²
Insulation	PVC	No. of wires	5
Material sheath	PVC	Sheath diameter, max.	8.1 mm
Sheathing colour	grey (similar to RAL 7001)		

Mechanical and material properties of cable

Min. bending radius, once only	4 x cable diameter

plug

Connector left	PushPull Power	Connector right	PushPull Power

Classifications

ETIM 6.0	EC000993	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90	eClass 8.1	27-06-91-90
eClass 9.0	27-06-20-01	eClass 9.1	27-06-23-90

Approvals

Approvals	EAC
ROHS	Conform

Creation date May 27, 2019 3:50:22 PM CEST

Industrial Ethernet
IE-CSPS5VS0010VAPVAP-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Downloads

Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN